




## **CARTONERS**

#### **EXPERTS FOR DIVERSE PRODUCTS IN CARTONS**

Uhlmann cartoners excel in terms of cost-efficiency, precision, and process reliability, and this proficiency is not restricted to packaging blisters in cartons. They are equally competent in handling bottles, pens, or pillow packs with product-related utensils, all types of leaflets, and cartons of critical quality at a consistently high output. Intermittent or continuous motion cartoners are available depending on your requirements.

These can be integrated into a line or used as standalone machines. Standard types of closure are possible with each of our cartoners: these include tuck-in and hot-melt closure, the use of a fourth flap, side loading with top opening, as well as tamper-evident options. All cartoners can be fitted with marking systems or Track & Trace functions, and can be linked to appropriate labeling systems.

### PRACTICE-ORIENTED AND PRODUCTIVE



#### C 2155

An intermittent motion cartoner. Easy to operate and suitable for small to medium batches of a wide range of solid and liquid dose products: bottles, vials, wallets, small plastic containers, ampoules, syringe blisters, inhalers, pillow packs, and medical devices.

#### C 2156/C 2206

Two continuous motion, 6"-pitch cartoners for the highly flexible packaging of a wide range of products in small and medium batches. Both models are suitable for all carton qualities.





#### C 2305/C 2504

Continuous motion cartoners offering a consistently high output of 300 and 500 cartons per minute respectively. Ideal for large batches. Easy to operate. Changeovers to a new format take a maximum of 15 minutes.



## **TECHNICAL DATA CARTONERS**

Cartoner	Max. output cartons/min.	Operating mode	Max. carton size [A × B × H]	Pitch	Max. blister stack height
C 2155	150.	intermittent	115 x 100 x 170 mm	140 mm	85 mm
C 2156	150	continuous	130 × 100 × 250 mm	6"	95 mm
C 2206	200	continuous	130 x 100 x 200 mm	6"	95 mm
C 2305	300	continuous	105 x 105 x 155 mm	5"	100 mm
C 2504	500	continuous	80 x 90 x 155 mm	4"	85 mm

# **ALL OPTIONS: TYPES OF CLOSURE**



1 Tuck-in closure with airplane flaps




Double-sided hot-melt closure



Tuck-in closure with reversed flaps



Hot-melt closure with fourth flap – reclosable



Combination tuck-in and hot-melt closure

THE HEARTBEAT OF PHARMA PACKAGING

Uhlmann Pac-Systeme GmbH & Co. KG Uhlmannstrasse 14–18 88471 Laupheim Germany Phone +49 7392 702-0 info@uhlmann.de To find your personal contact person and our locations worldwide please visit **www.uhlmann.de** 





